

Pushbutton, 15.2 mm, quick connector, momentary contact function, 1 NO, bezel black



fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology

special features

Drucktaster opak, nicht beleuchtbar
Einbaudurchmesser 15,2, mm
max. 250 V / 700 mA
Schraub- oder Flachstecker-Anschluss
Befestigungstechnik mit Gewinding
Schutzart IP 40 frontseitig (IP 65 mit Schutzkappe)



description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, solder/quick-connect terminal for 6.3 x 0.8 mm or 2 x 2.8 x 0.8 mm

technical data

> general

Bezel color	black
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
net weight	5 g
Operating life	25,000 cycles
B10	32,500 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 with sealing cap
MOQ order	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

> RAFI eCatalog

> mounting diameters

Outside dimension, length	19 mm
Outside dimension, width	19 mm
Outside dimension, height	29.7 mm
Mounting hole	15.2 mm

Mounting depth 21.5 mm

Installation height 8.2 mm

➤ **mechanical data**

Actuation function momentary contact function

Operating force, max. 7.5 N

Operating travel, max. 3 mm

Contact function 1 NO

Contact system Bridge contact

Contact material Silver

Fixing Threaded ring

Solderability No

Terminal on the rear Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8

➤ **electrical data**

Rated voltage, max. 250 V

Rated current, max. 0.7 A