

Mounting depth	21.5 mm
Installation height	8.2 mm
> mechanical data	
Actuation function	momentary contact function
Operating force, max.	7.5 N
Operating travel, max.	3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Solderability	No
Terminal on the rear	Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8
> electrical data	
Rated voltage, max.	250 V
Rated current, max.	0.7 A