

Pushbutton, 9.1 mm, 1NO+1NC, momentary contact function, 1 NC + 1 NO, bezel black



fields of application

> Mechanical and system engineering

> Model construction

> Home technology

special features

Drucktaster opak, nicht beleuchtbar

Einbaudurchmesser 9,1, mm

max. 24 V / 100 mA

Lötanschluss

Befestigungstechnik mit Gewinding

Schutzart IP 40 frontseitig



description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NC + 1 NO

technical data

> general		direct links
Bezel color	black	> RAFI eCatalog
Property of bezel / mushroom	opaque	
Collar shape	round	
Operating temperature, min.	-25 °C	
Operating temperature, max.	70 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	80 °C	
illuminated	No	
Soldering time for manual soldering, max.	3 sec	
Soldering temperature for manual soldering	350 °C	
Soldering	Manual soldering	
Packaging	Box	
Packaging unit	10 pcs.	
net weight	2.2 g	
Operating life	200,000 cycles	
B10	260,000 cycles	
Degree of protection, front side, according to DIN EN 60529	IP40	
MOQ order	50 pcs.	
RoHS compliant	Yes	
REACH compliant	Yes	
> mounting diameters		

Outside dimension, length	11 mm
Outside dimension, width	11 mm
Outside dimension, height	32 mm
Mounting hole	9.1 mm
Mounting depth	25 mm
Installation height	7 mm

> mechanical data

Actuation function	momentary contact function
Operating force, max.	5 N
Operating force, min.	5 N
Operating travel, max.	1.5 mm
Contact function	1 NC + 1 NO
Contact system	Bridge contact
Contact material	Gold
Fixing	Threaded ring
Solderability	Yes
Terminal on the rear	Solder terminal

> electrical data

Rated voltage, max.	24 V
Rated current, max.	0.5 A