

LED, FS technology QC Clip, 24 Volt, white



description

- > Clip with SMT LED
- > Illumination of illuminated pushbuttons, illuminated selector switches, illuminated emergency stop and illuminated actuators
- > Mounting: snap into switching elements QC and clip carrier for illuminated actuator
- > For better illumination use switching elements with light guide
- > For clear colors we recommend to choose the LED color in the color of the bezel

technical data

> general

Luminous element color	white
Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C
illuminated	Yes
Luminous elements	LED
Packaging unit	10 pcs.
net weight	1 g
MOQ order	10 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

> [RAFI eCatalog](#)

> mounting diameters

Outside dimension, length	18.2 mm
Outside dimension, width	7.98 mm
Outside dimension, height	17.23 mm

> mechanical data

Terminal on the rear	Flat quick-connect terminal 2.8 x 0.8
----------------------	---------------------------------------

> electrical data

Operating voltage of the luminous element, min.	19.2 V
Operating voltage of the luminous element, max.	28.8 V
Voltage type	DC
Rated operating voltage	19,2-28,8 V

Power loss	0.058 W
------------	---------