

NYS228C-*

3 pole 1/4" plug, diecast handle with color coding ring and rubber flex relief

*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue



Technical Information show hide

Product	
Title	NYS228C-*
Connection Type	Plug
Gender	male
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Contact resistance	depends on mating connector
Rated current	depends on mating connector
Mechanical	
Cable O.D.	≤ 6 mm
Lifetime	1000 mating cycles
Wiresize	24 AWG
Material	
Contact plating	2 μm Ni
Contacts	Brass (CuZn39Pb3)

Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Insulation	Thermoplastic
Strain relief	Crimp type SnCe plated

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	- 20 °C to +70 °C