

300V 16A 1.5m²

Specifications:

- Poles: 2, 3, 4, 5, 6, 8 and 10
- Pitch: 5mm
- Pin dimension: 1.0 x 1.0mm

Materials:

- Housing: PBT (30% Glass filled)
 Solder pin: Brass, tin plated
 Screw: M2.6, steel, zinc plated
 Wire protector: 0.2t, phosphor bronze, nickel plated



Order codes:

- 21-0440** (2-way – Black)
- 21-0442** (3-way – Black)
- 21-0444** (4-way – Black)
- 21-0445** (5-way – Black)
- 21-0446** (6-way – Black)
- 21-0447** (8-way – Black)
- 21-0448** (10-way – Black)

