

Measuring leads

MAL S GG-B 25/2,5



Product	MAL S GG-B 25/2,5
description	Safety adapter test lead according to IEC 61010 with 4 mm safety plug straight outlet and 4 mm safety socket on the other end. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve. Built in color indicator for easy identification of insulation damages.
operating instruction	BA453
article-no. / *colour	9340441xx ● 00 black ● 01 red ● 02 blue ● 03 yellow ● 04 green ● 88 yellow green Ni
drawing	
technical data	
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current (consider derating curve)	32 A
material plug	brass, nickel plated
material socket	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-2
cable length	25 cm
conductor size	2,5 mm ²
cable material	PVC

4 mm safety system

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges
stand: 13.06.2022

stand: 13.06.2022