


Measuring leads

MAL 2800 S



Product	MAL 2800 S
description	Safety adapter test lead with 4 mm safety plug with onward connection capability and 4 mm safety socket on the other end. The max. width of the plug is limited to 7.8mm. This is particularly suitable for applications on terminal blocks due to application-specific grid dimension.
operating instruction	BA453
article-no. / *colour	00 black 01 red Ni
drawing	
technical data	
rated voltage	AC/DC 300 V
measurement cat. acc. to IEC 61010	CAT III
rated current (consider derating curve)	32 A
material plug	brass, nickel plated
material socket	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C

4 mm safety system

inflammability class acc. to UL 94 (only valid for basic material of housing)	V-2
cable length	8 cm
conductor size	2,5 mm ²
cable material	PVC

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges
 stand: 09.06.2022

stand: 09.06.2022