

Plugs



KST 14/4



Product	KST 14/4
description	Jumper plug with spring-loaded 4 mm plugs and shatter-proof insulation, not stackable.
operating instruction	BA416
article-no. / *colour	9722671xx ● 00 black Ni
drawing	
technical data	
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	32 A
material plug	brass, nickel plated
housing material	PBT
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to 70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022