


Test probes

MZS 1 - Pruef



Product	MZS 1 - Pruef
description	Needle shaped, long stainless steel test probe with shatter-proof insulated sleeve and unsprung 4 mm contacting socket. During state of connection or operation of test leads, it is possible to measure with the test probe from the back side of the closed connector.
operating instruction	BA419
article-no. / *colour	9736011xx  00 black  01 red Ni
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	1 A
material socket	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-20 °C to +60 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022