


LOC J	DIST —	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			G	REVISED	26JUN2014	Z.S	N.Y	





NOTES

1 MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC ,POLYESTER(94V-0), COLOR:1-/2-/3- : BLACK : 9- : NATURAL


2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON

3. APPEARANCE CRITERIA IS BASED ON TE CRITERIA.



 KEYING:Z 3-1318118-9	 KEYING:Z 3-1318118-6	 KEYING:Y 2-1318118-9 9-1318118-9	 KEYING:Y 2-1318118-8 9-1318118-8	 KEYING:Y 2-1318118-6 9-1318118-6
 KEYING:X 1-1318118-9	 KEYING:X 1-1318118-8	 KEYING:X 1-1318118-6		

	—	5.58	26.4	25.8	22.5	9	20	3-1318118-9
OBSOLETE		5.58	26.4	25.8	22.5	9	20	5-1318118-9
	—	5.58	26.4	25.8	22.5	9	20	9-1318118-9 2-1318118-9
	—	5.58	26.4	25.8	22.5	9	20	1-1318118-9
	—	4.69	21.4	20.8	17.5	7	16	9-1318118-8 2-1318118-8
	—	4.69	21.4	20.8	17.5	7	16	1-1318118-8
OBSOLETE		3.8	16.4	15.8	12.5	5	12	5-1318118-6
	—	3.8	16.4	15.8	12.5	5	12	3-1318118-6
	—	3.8	16.4	15.8	12.5	5	12	9-1318118-6 2-1318118-6
	—	3.8	16.4	15.8	12.5	5	12	1-1318118-6
FINISH	NET WEIGHT(g)	C	B	A	N	POS	PART NUMBER	



KEY LOCATION VIEW
2-1318118-6
9-1318118-6
(KEYING Y)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

± 10
± 30
± 100

± 0.3
>10 : ± 0.35
>30 : ± 0.4

± 3°

DWN
K.IKEDA
CHK
N.MATSUBARA
APVD
I.HASEGAWA
PRODUCT SPEC
108-5619
APPLICATION SPEC
114-5258
WEIGHT

07DEC1998
07DEC1998
07DEC1998

STE

TE Connectivity

DOUBLE ROW REC HSG
DYNAMIC D-2100D

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1318118

RESTRICTED TO
—

SCALE
4:1

SHEET
1 OF 1

REV
G

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
G