




- 1

RCPT ACCEPTS SIZE 20 DF SOCKET CONTACTS. CONTACTS MUST BE PURCHASED SEPARATELY.
- 2

ALL PARTS SHIPPED UNASSEMBLED.
- 3

FLAME RETARDANT 94V-0 RATED, STYRENE POLYOLEFIN OR PVC, BLACK.
- 4

INSERT - FLAME RETARDANT 94V-0 RATED GLASS FILLED, NYLON OR POLYESTER, BLACK.
- 5

SHELLS & SHIELDS - STEEL PER ASTM A109.
- 6

SHELLS & SHIELDS - .000200 MIN TIN PLATE OVER .000100 MIN COPPER UNDERPLATE.
- 7

COMPONENTS INDIVIDUALLY BULK PACKED.
- 8

CARBON STEEL, C1022.
- 9

ZINC NICKEL, TRIVALENT BLACK.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

3 4 5 8

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.020
4 PLC	±	-
ANGLES	±	-
FINISH	6 9	

APVD
M.WALMSLEY

PRODUCT SPEC
108-40030

APPLICATION SPEC
114-40030

WEIGHT
-

CUSTOMER DRAWING

DWN
J.REITZEL

CHK
S.BOLASH

APVD
M.WALMSLEY

31JUL03

TE Connectivity

BULK KIT, RCPT, SHIELDING ENCLOSURE, SIZE 3, 25 POSN, AMPLIMITE HDP-20

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1658658

RESTRICTED TO
-

SCALE
2:1

SHEET
1 of 1

REV
C