



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **2**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Black**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	2
--	---

Body Features

Crimp Terminal Housing Housing Color	Black
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Length	31.5 mm[1.24 in]
Crimp Terminal Housing Centerline	7.4 mm[.291 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	3000
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability






Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 964586-1 FF 2P HOUSING TAB POLYESTER VALOX 357	 TE Part # 170340-1 FF 250 TAB 20-14AWG BR WITHOUT LATCH	 TE Part # 170341-3 FF 250 TAB 14-12AWG PTBR WITHOUT LATCH	 TE Part # 170349-2 FF 250 TAB 22-20AWG TPBR WITHOUT LATCH
 TE Part # 170340-3 FF 250 TAB 20-14AWG PTBR WITHOUT LATCH	 TE Part # 170341-1 FF 250 TAB 14-12AWG BR WITHOUT LATCH	 TE Part # 928193-1 FF 2.8MM TAB HSG 2P PBT BLACK	 TE Part # 626065-5 HOUSING 2P .110 FASTIN-ON TAB
 TE Part # 170349-1 FF 250 TAB 22-20AWG BR WITHOUT LATCH	 TE Part # 626057-1 FASTIN-ON .110 HOUSING TAB NYLON 6/6	 TE Part # 180908-3 FF 250 TAB HSG 2P NYLON BLUE	 TE Part # 626063-1 FASTIN-ON .110 HOUSING TAB PA 6.6
 TE Part # 927203-1 FF 250 TAB HSG 2P NYLON BLACK	 TE Part # 964473-1 FF 110 TAB HSG 10P PBT BLACK		

Also in the Series | FASTIN-FASTON 250





Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)



PCB Terminals(2)



Quick Disconnects(258)

Customers Also Bought




TE Part #160450-2
FF 250 TAB 18-14AWG TPPB



TE Part #1-967622-5
TIMER, CONNECTOR HOUSING



TE Part #DT06-2S-EP11
DEUTSCH DT Series Housings & Connectors




TE Part #160660-2
SPLICE 22-18 AWG .013 TPBR



TE Part #1534027-1
MQS VERRIEGLUNG F2P



TE Part #160644-3
SPLICE 20-15 AWG .016 TPBR



TE Part #1-174930-1
070 MLC W-W CAP HSG 6P F/A

Documents

Product Drawings
FF 250 TAB HSG 2P NYLON BLACK
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_180908-5_AB.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_180908-5_AB.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_180908-5_AB.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

UL Report

English