



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1579007-1
AUSDRUECKWERKZEUG

TE Part # 1976143-1
SDE COMMERCIAL TOOL OR DIE

TE Part # 539727-2
DIE MCP2,8/1,5-4EDS

TE Part # 1-1579007-2
EXTRACTION TOOL

TE Part # 1976143-2
PRO-CRIMPER DIE

TE Part # 2063624-1
SDE MCP2.8 0.5-1.0mm2 ASSY

TE Part # 2063624-2
SDE MCP2.8 0.5-1.0mm2 DIE

TE Part # 2304643-1
49POS, HYBRID, REC HSG ASSY, SLD

TE Part # 2304643-2
38POS, HYBRID, REC HSG ASSY, SLD

TE Part # 2304643-3
27POS, HYBRID, REC HSG ASSY, SLD

TE Part # 2304643-4
60POS, AMP MCP 2.8, REC HSG ASSY, SLD

TE Part # 539726-2
DIE-MCP2,8/0,5-1EDS

Also in the Series | AMP MCP 2.8

Automotive Connector Caps & Covers
(1)

Automotive Connector Locks &
Position Assurance(6)

Automotive Headers(1)

Automotive Housings(179)

Automotive Seals & Cavity Plugs(1)

Automotive Terminals(6)

Insertion & Extraction Tools(6)

Module Components(1)

Also in the Series | AMP MCP Connector System



Automotive Connector Caps & Covers (24)

Automotive Connector Locks & Position Assurance(8)

Automotive Headers(29)

Automotive Housings(352)

Automotive Seals & Cavity Plugs(6)

Automotive Terminals(124)

Insertion & Extraction Tools(13)

Other Automotive Connector Accessories(2)

Customers Also Bought

TE Part #3-643817-7
07P MTA156 CONN ASSY 18AWG ORA

TE Part #1879499-3
CRGH2010 5% 1R2 1W

TE Part #1743282-1
MQS, CONNECTOR HOUSING

TE Part #1-967590-1
AMP MCP, RECEPTACLE AND TAB

TE Part #2292799-3
AMPSEAL 16 BACKSHELLS

TE Part #1355437-1
MCP9,5 EINZELDICHTG

TE Part #1-968876-1
AMP MCP 2.8, CONTACT SWS (LP)

TE Part #1241381-3
AMP MCP 1.5K, CONTACT, SWS, (LP)

TE Part #HDP26-24-16PE-L017
PLG, 16P, BLK, E, RNG, 12, P

Documents



CAD Files

Customer View Model

ENG_CVM_1-968875-2_J3.3d_igs.zip

English

Customer View Model

ENG_CVM_1-968875-2_J3.3d_stp.zip

English

Customer View Model

ENG_CVM_1-968875-2_J3.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HDSCS Catalog

English

CONNECTOR SELECTOR

English

Product Specifications

AMP MCP 2.8, CONTACT APPLICATION SPECIFICATION

English

Product Specification

English