



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >
DYNAMIC 2000 REC AND TAB HSG



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **2.5 mm [.098 in]**

[All DYNAMIC 2000 REC AND TAB HSG \(54\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	Black



Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D9934-A66
DYNAMIC 2000 CONTACT



TE Part # CAT-D9934-A66B
DYNAMIC 2000 HDR ASSY



Also in the Series

Dynamic 2000 Series

Insertion & Extraction Tools(1)	PCB Connector Mounting(4)	PCB Terminal Blocks(23)	Wire-to-Board Connector Assemblies & Housings(54)
Wire-to-Board Connector Contacts(10)	Wire-to-Board Headers & Receptacles (44)		

Customers Also Bought

TE Part #1318095-2 DYNAMIC 3500 REC AND TAB HSG	TE Part #316041-6 DYNAMIC 5000 REC AND TAB CONT	TE Part #1-178128-3 DYNAMIC 3200 REC AND TAB HSG	TE Part #1-1318120-3 DYNAMIC 2000 REC AND TAB HSG
TE Part #1-175218-5 DYNAMIC 3000 CONTACT	TE Part #1-917807-2 DYNAMIC 5000 REC AND TAB HSG	TE Part #1-178288-3 DYNAMIC 3100 REC AND TAB HSG	TE Part #1318107-1 DYNAMIC 2000 CONTACT

Documents

Product Drawings

DYNAMIC D-2 REC HSG 3P Z-KEY

Japanese

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_3-1318120-3_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1318120-3_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1318120-3_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH](#)

English

Product Specifications

[Dynamic Connector D-2000 Series](#)

Japanese

[Application Specification](#)

Japanese

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[Agency Approval Document](#)

English