









REV
NC DTMH04-3P*

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P19881	9-15-08	SB

8 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

7. RECEPTACLE IS RATED AT 150°C.

6. MATERIAL - HOUSING: PLASTIC; GROMMET: RUBBER.

5. THIS RECEPTACLE MATES WITH DTMH06-3S-**** AND DTM06-3S-**** PLUG. (**** = ALL MODIFICATIONS)

4 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

3 TERMINAL POSITION ASSURANCE (TPA) LOCK PRE-MOUNTED: WMH-4P* (* = A,B,C,D KEYS).

2. DIMENSION TOLERANCE: $\pm .025$ [.64].

1. DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.5]









SIGNATURE & DATE	
DR	J. APOSTOL 28DEC2007
CHK	B. S. 9/14/08
PE	A. Whitacre 8/1/08
APPD	D. Meyer 9/2/08
SCALE	NONE

RECEPTACLE
3 PIN CONT. #20
COLOR: BLACK
DTMH SERIES

ENVELOPE

EP 180	MATL. CODE
3850 INDUSTRIAL AVE. HEMET, CA 92545	
DEUTSCH INDUSTRIAL	
B	DTMH04-3P*
DWG SIZE	CODE 11139 SHEET 1 OF 2

REV NC	DTMH04-3P*	REVISIONS			
		SYM	DESCRIPTION	DATE	APPROVED
			SEE SHEET 1	9-15-08	SB



DTMH04-3PA
-A- KEY
TPA COLOR: GREY

DTMH04-3PB
-B- KEY
TPA COLOR: BLACK

DTMH04-3PC
-C- KEY
TPA COLOR: GREEN

DTMH04-3PD
-D- KEY
TPA COLOR: BROWN

NOTES:

SIGNATURE & DATE		RECEPTACLE 3 PIN CONT. #20 COLOR: BLACK DTMH SERIES	EP 180		MATL. CODE
DR	J. APOSTOL 28DEC2007		 3850 INDUSTRIAL AVE. HEMET, CA 92545		 DTMH04-3P*
CHK	<i>[Signature]</i> 9/10/08				
PE	<i>[Signature]</i> 8/1/08				
APPD	<i>[Signature]</i> 9/12/08	ENVELOPE	 DTMH04-3P*		CODE 11139
SCALE	NONE				