



TOOLCRAFT

DATASHEET

Flexible Magnetic Rubber

Version 03/17

Item no. : 1524016



Dimension

Item	Length	Width	Thickness
2285710	148mm	210mm	0.8mm

Material Properties

Tensile Strength	Elongation	Hardness
>2.0 mPa	20%	30 - 40

Color Brown Black

Surface Finishing 1 side with 3M 9448 Adhesive; Magnetic side with UV coating

Packaging Polybag with sticker

Material Grade..... Isotropic EP-7(C)

Density 3.65 - 3.75 g/cm³

Magnetizd..... 1 side multipole (Pole Pitch: 3.0mm)

Operation Temperature ≤ 60°C

Optimum Storage Temperature and Humidity 21°C and 50% relative humidity