

# PRODUCT DATA SHEET

**3544a**

**Pressed cable terminal uninsulated – Ring shape – 3544 A Cu sn 4-10**



## Product Overview

SKU	3544a
Part description	Pressed cable terminal uninsulated – Ring shape
Part designation	3544 A Cu sn 4-10

### Material

Component	Copper
Surface	pure tin-plated

### Technical Details

Net weight kg/1000	2.932
Conductor cross-section	10mm <sup>2</sup> / AWG 8
Maximum electrical rating AWG8	70A

### Markings

Approved UL	E235797
-------------	---------

### Dimensions

for bolt	M4
A [mm]	8.00
D [mm]	4.30
D1 [mm]	4.50
D3 [mm]	12.00
L [mm]	18.00
R [mm]	6.50
S [mm]	1.20

