

Type designation: AG3/LR41

Chemical system: Zn/KOH-H₂O/MnO₂

Nominal voltage: 1.5 V

Weight: Approximate 0.7 g

The dimensions shall be in accordance with the below figures both prior to and after the service output test.

Dimension (mm)

Designation	AG3/LR41
Diameter	7.55~7.90
Height	3.30~3.60

Capacity:

Designation	AG3/L41
Approximate Capacity (mAh)	35

Operating temperature: 10°C ~ 25°C

Recommend storage temperature: 20°C ± 2°C

Shelf lifetime: 3 Years