

**W-Series
IH 6.3 WEM GE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	IH 6.3 WEM GE
Order No.	0386260000
Version	W-Series, Insulating sleeve
GTIN (EAN)	4008190164256
Qty.	100 pc(s).

W-Series
IH 6.3 WEM GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	9 mm	Width (inches)	0.354 inch
Height	30 mm	Height (inches)	1.181 inch
Depth	4.5 mm	Depth (inches)	0.177 inch
Net weight	0.46 g		

Temperatures

Operating temperature, min.	-50 °C	Storage temperature, max.	40 °C
Storage temperature, min.	10 °C	Operating temperature	-50 °C...
Storage temperature	10 °C...40 °C	Continuous operating temp., max.	100 °C

Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-2		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

UL rating data

Certificate No. (UR)	E60693
----------------------	--------

Classifications

ETIM 3.0	EC000897	ETIM 4.0	EC000897
ETIM 5.0	EC000897	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
------------------	----------------------