

Connecting elements
H1,5/14 R SP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- Polypropylene conical cable entry funnel
- Heat-resistant up to 105°C
- Entry funnel can also be manufactured from a non-flammable material on request

For conductors from 0.14 – 150 mm² (AWG 26-300 MCM)

Material: E-Cu, tin galvanised

Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

Type	H1,5/14 R SP
Order No.	1476270000
Version	Wire-end ferrule, insulated, 10 mm, 8 mm, red
GTIN (EAN)	4050118283099
Qty.	100 pc(s).

Data sheet

**Connecting elements
H1,5/14 R SP**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	14 mm	Width (inches)	0.551 inch
Net weight	0.026 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	3.5 mm	Colour code	Weidmüller
Conductor cross-section	1.5 mm ²	Contact surface diameter (D1)	1.7 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 16

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01	eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [EPLAN](#)