

An unparalleled combination of chemical splash protection, comfort and durability

- **World leader:** TouchNTuff® 92-600 gloves are the world's leading disposable gloves for chemical splash protection
- **Superior protection:** Made with TNT™ Chemical Splash Resistance Technology, these gloves effectively safeguard hands from exposure to harmful chemicals
- **Elevated comfort:** Super soft nitrile provides a comfortable feel during extended wear
- **Robust durability:** EN388 certified, meeting level 1 abrasion to prevent ripping and tearing during heavy-duty work
- **Prevents surface defects:** Silicone-free, they prevent contaminant transfer that causes flaws in paints, coatings and finishes
- **Certified harm-free:** Dermatest® certification ensures these PPE gloves are skin-friendly



Industries

- Life Sciences
- Food Processing
- Automotive
- Agriculture
- Infrastructure Maintenance
- Chemical

Recommended For

- Transferring liquids and solids
- Meat, Fish and Food Processing
- Industrial Production
- Maintenance
- Laboratory analysis
- Chemical Handling

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile
External Glove Surface	Smooth
Audit Standards	ISO 9001
Product Certification	Category III, EN 388:2016 1XXXX, EN ISO 21420:2020, EN ISO 374-1:2016 Type B JKPT, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, EU Food Contact Approved, ISO 18889:2019, ISO 9001, UKCA, DOSH-SIRIM certified, Dermatest
Packaging Overview	XS-XL: 100 gloves per dispenser, 10 dispensers per case, 1000 gloves per case XXL: 90 gloves per dispenser, 10 dispensers per case, 900 gloves per case Size XS and XXL are not available in China and Brazil Vend Pack Variant (Size S, M, L, XL): 20 gloves per box, 24 boxes per carton
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Product Segmentation	Robust
Antistatic	Yes EN1149
Vulcanization Chemical Accelerators	Zinc Dibutyldithiocarbamate (ZDBC) <i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i>


PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.45		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	4.0 AQL (North & South America, except Brazil) / 1.5 AQL (Europe, Middle East, Africa, Asia, Pacific, Brazil)		ASTM D5151,EN 455-1
	BEFORE AGING	AFTER AGING	
Elongation at Break (%)	≥ 600	≥ 525	ASTM D412
Force at break (N)	≥ 10	≥ 10	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	92600060	92600070	92600080	92600090	92600100	92600110

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region
MY +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region
BR +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Ansell PYC
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

