

BLAUPUNKT CHARGER C4 PRO

BL-C4PROCH/1VH

KEY FEATURES

- ✓ **100 years of brand history**
Rich heritage & German quality
- ✓ **Fast charging - only 1 hour***
- ✓ **USB cable included**
4x AA 2000 mAh included
- ✓ **LCD display** with charging status
- ✓ **Charges 1-4 Ni-MH cells (AA or AAA)**
- ✓ **Delta V Cut Off** system to prevent overcharging
- ✓ **High-performance battery charger** with high quality fabric and materials



LOGISTIC INFORMATION	Model name: BL-C4PROCH/1VH; Code: 30010281; EAN CSU: 5410853069591; EAN CAR: 5410853069669; CSU per CAR: 8 CSU;
SLOTS	4-slots AA/AAA
CHARGING TIME	1 hour*
DIMENSIONS	CHARGER size and weight: 69.5mm x 100mm x 24.5mm 221.9g; CSU size and weight: 84mm x 130mm x 37mm 270.9g;
INPUTS / OUTPUTS	Input: mirco USB/Type C 5V/2A; Output: AA 3600 mA (1pc) 1800 mA (2pcs) 900mA (3-4pcs) Output: AAA 1800mA (1pc) 900 mA (2pcs) 4500mA (3-4pcs)
OTHER	Large LCD display Individual charging control Alkaline battery and bad cell detection Short circuit protection



RELIABLE, REUSABLE ENERGY

With Blaupunkt PRO Charger, you'll always have a fully charged, reliable power source to hand.

Charge up to 4AA or AAA batteries in as little as 1 hour* to keep household devices such as game controller, toys, and remote controls consistently powered.



PORTFOLIO COMPARISON



BL-C4CH/1VH



BL-C4PROCH/1VH

CHARGING TIME	8-10 hours	1 hour
SLOTS	4-slots AA/AAA	4-slots AA/AAA
IMPUTS / OUTPUTS	Input: mirco USB 5V/1A; Output: AA 300 mAh (1-4pcs) Output: AAA 120mAh (1-4pcs)	Input: mirco USB/Type C 5V/2A; Output: AA 3600 mA (1pc) 1800 mA (2pcs) 900mA (3-4pcs) Output: AAA 1800mA (1pc) 900 mA (2pcs) 4500mA (3-4pcs)
OTHER	Including 4xAA rechargeables 2000 mAh Including USB-A to micro USB cable	Including 4 x AA rechargeable 2000 mAh Including USB-A to micro USB cable Large LCD display