

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJC 04/27/05'	~~~~~	卢金春
B	图面绘制错误	LL 10/29/06'	~~~~~	卢金春
C	整理图面	YCH 04/24/08'	~~~~~	

NOTES:

1. ELECTRICAL CHARACTERISTICS:

- 1.1 CONTACT RESISTANCE: 20mΩ Max. INITIAL.
- 1.2 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
- 1.3 INSULATION RESISTANCE: 1000MΩ Min.

2. ENVIRONMENT CHARACTERISTICS:

- 2.1 TEMPERATURE: -40°C~+105°C.

3. PRODUCT NUMBER CODE:

DS1011-01- X X X X X

LOCK DIM.

8: 8.60mm(standard latch)

2: 4.20mm(short latch)

S: 4.2mm(special latch)

HOUSING COLOR

B: BLACK

A: GRAY

CONTACT PLATING

Ti: SELECTIVE GOLD FLASH

Si: FULL GOLD FLASH

HOUSING TYPE

S: SMALL LATCH HOUSING

MOUNTING TYPE


S: STRAIGHT

R: R/A

No.OF CONTACTS



10 14 16 20 26 30

34 40 50 60 64




V/T TYPE

R/A TYPE




AVAILABLE DIMENSION TABLE


No.of Contacts	10	14	16	20	26	30	34	40	50	60	64
A	31.92	37.00	39.54	44.62	52.24	57.32	62.40	70.02	82.72	95.42	100.50
B	21.72	26.80	29.34	34.42	42.04	47.12	52.20	59.82	72.52	85.22	90.30
C	10.16	15.24	17.78	22.86	30.48	35.56	40.64	48.26	60.96	73.66	78.74
D	18.22	23.30	25.84	30.92	38.54	43.62	48.70	56.32	69.02	81.72	86.80



SPECIAL LATCH



SHORT LATCH



STANDARD LATCH

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	mm	TITLE
X.	±0.60	X.	±5°	UNITS	mm	SHOULDED HEADER PITCH 2.54mm
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES DS1011-01 SERIES
.XX	±0.25	.XX	±2°			
DRAWING TYPE	CUSTOMER					
SCALE	1:1	SHEET	1 OF 1			
DRAWING NO.	C-DS1011-01-XXSXXX					



晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD