

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJC 04/27/05'	~	卢金春
B	ADD DIM	LL 09/21/06'	~	卢金春
C	HOUSING CHANGE	YCH 04/09/08'	~	卢金春
D	Drawing correction	YCH 07/06/09'	~	卢金春
E	ADD P/N CODE	YCH 12/02/13'	~	LJC 12/02/13'
F	Drawing correction	JLZ 02/10/15'	~	

NOTES:

1. ELECTRICAL CHARACTERISTICS:

- 1.1 CONTACT RESISTANCE: 20mΩ Max. INITIAL.
- 1.2 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
- 1.3 INSULATION RESISTANCE: 1000MΩ Min.

2. ENVIRONMENT CHARACTERISTICS:

- 2.1 TEMPERATURE: -40°C~+105°C.

3. PRODUCT NUMBER CODE:

DS1011- X X X X X X - X

PLATING LEVEL(FOR GOLD ONLY) ⑤
B: LEVEL B

LOCK DIM.
7: 7.90mm(standard)
4: 4.50mm(special)

HOUSING COLOR
B:BLACK
A:GRAY

CONTACT PLATING
Si: Full Gold flash

HOUSING TYPE
B: BIG LATCH HOUSING

MOUNTING TYPE
S: STRAIGHT
R: R/A





No.OF CONTACTS
10 14 16 20 26 30
34 40 50 60 64

AVAILABLE DIMENSION TABLE

No.of Contacts	10	14	16	20	26	30	34	40	50	60	64
A	32.1	37.18	39.72	44.80	52.42	57.50	62.58	70.20	82.90	95.60	100.68
B	22.20	27.28	29.82	34.90	42.52	47.60	52.68	60.30	73.00	85.70	90.78
C	10.16	15.24	17.78	22.86	30.48	35.56	40.64	48.26	60.96	73.66	78.74
D	18.10	23.18	25.72	30.47	38.42	43.50	48.58	56.20	68.90	81.60	86.68

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°
DRAWING TYPE		CUSTOMER	
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1011-XXBXXX-X-F		

PROJECTION	UNIT	TITLE
⊕	mm	2.54mm SHROUDED HEADER R/A & V/T TYPE
SHEET SIZE	SERIES	
A4	DS1011 SERIES	
 晨翔电子有限公司 CONNFLY® CONNFLY ELECTRONIC CO., LTD		




R/A TYPE V/T TYPE

R/A TYPE

Latch Type	DIM.	E
Standard Latch	3.70	

V/T TYPE

Latch Type	DIM.	F
Standard Latch	3.10	
Standard Latch	8.10	



STANDARD LATCH

SPECIAL LATCH

FIGURE A