

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 03/11/11'		

NOTES:

1. MATERIAL

- 1.1 INSULATOR:THERMOPLASTIC(UL 94V-0).
- 1.2 CONTACT: COPPER ALLOY.

2. SPECIFICATION

- 2.1 TEMPERATURE RANGE:-40-105°C.
- 2.2 CONTACT RESISTANCE:30mΩ max.
- 2.3 INSULATION RESISTANCE:1000MΩ min.
- 2.4 DIELECTRIC WITHSTANDING VOLTAGE:AC 500V PER MINUTE.

3. PRODUCT NUMBER CODE:

DS1015-01- X X X

CONTACT PLATING
2: NICKEL + GOLD FLASH
6: Full Tin
8: Full GOLD FLASH

HOUSING COLOR
R:RED

No. OF CONTACTS
04 06 08 10 12
14 16 18 20 24

COVER

HOUSING

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	RED IDC SERIES	
X.	±0.60	X.	±5°	UNITS	mm	(MICRO MATCH CONNECTOR)		
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1015-01 SERIES	
.XX	±0.25	.XX	±2°					
DRAWING TYPE		CUSTOMER		 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
SCALE		1:1	SHEET					1 OF 1
DRAWING NO.		C-DS1015-01-XXX						



晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD