




REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 06/14/07'	~	LJC 06/14/07'
B	新增螺丝规格	YCH 11/05/11'	~	LJC 11/05/11'
C	DRAWING UPDATE	JLZ 08/08/17'	~	

NOTES: 备注

1. PRODUCTS PERFORMANCE:

- 1.0 VOLTAGE RATING: 250V AC.
- 1.1 CONTACT CURRENT RATING: 1.5A MAX. PER PIN.
- 1.2 CONTACT RESISTANCE: 20mΩ MAX.
- 1.3 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
- 1.4 INSULATION RESISTANCE: 1000MΩ MIN.
- 1.5 OPERATING TEMPERATURE: -40°C~+105°C.

2. PRODUCT NUMBER CODE:

DS1037 -01- X X X X X X X X

- SCREW DIM. E
4: 4.80mm
5: 5.80mm
⑥ 6: 4.80mm(Inside thread M2.6*0.45p, outside thread unc#4-40)
⑥ M3: 4.80mm(Inside thread M3.0, outside thread unc#4-40)
- BOARD LOCK DIM. F
7: 3.70mm
- CONTACT PLATING
T: SELECTIVE GOLD FLASH
Si: FULL GOLD FLASH
6: FULL TIN
- COLOR OF HOUSING
K: BLACK
B: BLUE
- SCREW TYPE
A: WITH SCREW TYPE
B: WITH RIVET TYPE
C: WITH SCREW AND RIVET TYPE
D: RIVET TYPE WITH SCREW IN BULD PACKAGE
- SHELL PLATING
N: Nickel
T: Tin
- CONNECTOR TYPE
M: MALE
F: FEMALE
- No. OF CONTACT
09: 9pos.
15: 15pos.
25: 25pos.
37: 37pos.

Dimension

Position	A±0.2	B±0.2	C±0.2	D
9	17.90	24.99	30.80	16.33
15	26.50	33.32	39.14	24.66
25	40.00	47.04	53.04	38.38
37	56.50	63.50	69.32	54.84

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.50	X.	±3°
.X	±0.30	.X	±2°
.XX	±0.20	.XX	±1°
DRAWING TYPE		ASSEMBLY	
SCALE		1:1	SHEET 1 OF 1
DRAWING NO.		C-DS1037-01-XXXXXXX-C	

PROJECTION	TITLE	D-SUB RIGHT ANGLE(9.4mm) TYPE	
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1037-01 SERIES
 晨翔电子有限公司			
CONN-FLY CONN-FLY ELECTRONIC CO. LTD			