



CP-BV6-R

cPot Strip

The cPot Strip is a compact ruggedized distribution box for mobile grounding / potential equalization applications. Rugged EASYLEN® housing is ideally suited for outdoor usage and demanding applications under harsh conditions. 6x cPot male IN / OUT.

Features & Benefits

- Extreme robust and safe EASYLEN® housing with leather grain texture
- High outdoor protection (IP54, IK, ..),
- Versatile mounting options
- M10 thread at the bottom
- Flame retardant (UL94-V2) and non-conductive housing material
- Light weight and compact housing design
- Stainless steel screws

Article Variations

Article name	Details	Order code
CP-BV6-R	cPot Strip. 6x cPot [m]	1027377

Technical Information

Product

Description	CP-BV6-R
-------------	----------

Electrical

Conductor cross section	Earth bar
-------------------------	-----------

Mechanical

Lifetime	> 500 Mating cycles per connector
Locking device	Latch lock
Dimension	220 x 77 x 61 mm

Material

Housing	Easylen®
Color	black

Environmental

Standards compatibility	UL94-V2
Protection class	IP54 in mated condition
Temperature range	-40 °C to 50°C