


Hygro-Thermometer Clock

 **Triple display with Clock, Temperature and Humidity**
With user settable clock alarm

Features:

- Attractive design for desktop or wall mounting
- Three LCD displays of Time, Temperature and Humidity
- Max/Min memory with reset for Temperature and Humidity
- Switchable °C or °F temperature display
- 12/24 hour Clock with alarm function
- Complete with built-in tilt stand, wall mounting bracket and AAA battery



Specifications:	445702
Humidity range	10 to 85%
Basic RH accuracy	± 6%
Temperature range	14 to 140°F (-10 to 60°C)
Basic Temperature Accuracy	1.8°F/1°C
Dimensions	4.3 x 2.8 x 0.8" (109 x 71 x 20mm)
Weight	4oz (113g)

Ordering Information:

445702Hygro-Thermometer Clock
409992Vinyl Pouch Carrying Case

