



POWERBANK F10000 I 20 W

Mobiler Zusatzakku

Technische Informationen

Akku:	10000 mAh
Farben:	Lila, Grau, Blau, Grün, Orange & Gelb
Batterietyp:	Lithium-Polymer Akku
Anschlüsse:	Output USB-A: 5,0 V/DC 3,0 A USB-A QC: 5,0 V/DC 3,0 A, 9,0 V/DC 2,0 A, 12,0 V/DC 1,5 A (max. 18,0 W) USB-C Out: 5,0 V/DC 3,0 A USB-C PD Out: 5,0 V/DC 3,0 A, 9,0 V/DC 2,22 A, 12,0 V/DC 1,67 A PPS: 5,0 – 5,9 V/DC 3,0 A 5,0 – 11,0 V/DC 2,0 A (max. 20,0 W) USB-A + USB-C Out: 5,0 V/DC 3,0A gesamt Input USB-C In: 5,0 V/DC 3,0 A USB-C PD In: 5,0 V/DC 3,0 A, 9,0 V/DC 2,0 A (max. 18,0 W)
Anzeige:	Digitale Prozentanzeige
Eigenschaften:	Überspannungsschutz, Entladeschutz, Überladeschutz, Kurzschlussicherung
Zubehör:	USB-C zu USB-C Ladekabel (unterstützt Power Delivery), Schlaufe
Abmessungen	131 x 67 x 15 mm
Gewicht:	222 g

Artikeldaten

Farbe	Art.-Nr.	EAN	VPE
Lila	7332033	4 034303 034284	2 Stück
Grau	7332034	4 034303 034192	
Blau	7332035	4 034303 034222	
Grün	7332037	4 034303 034253	
Orange	7332038	4 034303 034314	
Gelb	7332039	4 034303 034345	

(Intenso)[®]
for everyday life

QUALITÄTSPRÜFUNG
In Deutschland getestet ✓



* Für Details besuchen Sie bitte die folgende Webseite: <https://www.qualcomm.com/products/snapdragon/quick-charge>

Qualcomm® Quick Charge™ is a product of Qualcomm Technologies, Inc. Qualcomm is a trademark of Qualcomm Incorporated, registered in the United States and other countries. Quick Charge is a trademark of Qualcomm Incorporated. All Qualcomm Incorporated marks are used with permission.