



ENERGY ULTRA CR2032

Lithium button cell

Technical details

Battery type:	Lithium button cell (free of mercury, cadmium & lead)
Battery size:	CR2032
Chemical system:	Lithium / Manganese dioxides (Li/MnO ₂)
Normal voltage:	3V
Nominal capacity:	220 mAh
Reference standard:	2006/66/EC, IEC60086-1-2, IEC60086-4
Shelf life:	5 years
Weight:	2,9 g
Diameter:	19,7 -20 mm
Height:	2,9 - 3,2 mm

Battery marking

Type:	CR2032, Lithium
Brand:	Intenso Energy Ultra
Normal voltage:	3V
Polarity:	+

Product data

Volume	Article number	EAN	Packaging unit
6pcs blister	7502436	4034303027897	10 pieces
10pcs blister	7502430	4034303028535	

6pcs blister:



10pcs blister:

