



ENERGY ECO AA - HR6 - 2100 mAh

Rechargeable NiMH battery

Technical details

Battery type:	Nickel metal hydride (NiMH)
Battery size:	IEC: HR6, ANSI: AA
Chemical system:	Nickel metal hydride
Normal voltage:	1.2V
Nominal capacity:	2100 mAh
Reference standard:	2006/66/EC, IEC 61951-2
Life cycles:	Up to 1000
Weight:	27 g
Diameter:	14,5 mm
Height:	50,5 mm

Battery marking

Type:	AA, Mignon, HR6, 2100 mAh, NiMH
Brand:	Intenso Energy Eco
Normal voltage:	1.2V
Polarity:	+ or -
Warning:	Observe the correct polarity. Do not misuse. Rechargeable.

Product data

Volume	Article number	EAN	Packaging unit
4pcs blister	7505524	4034303029136	5 pieces

4pcs blister:

