

Technical data sheet

Load monitoring · LOCC-Box Accessories

Insulated jumper combs 16-pin



Identification

Type	LOCC-Box-BKW 7-6438
Part No.	716438

Product version

Datasheet version	02
-------------------	----

General

Accessories	Jumper comb 16-pin white
Connection type	Plug-in
Contact design	Flat contact 0.5 mm
Pin spacing	8.3 mm
Contact material	FeZn
Material	PVC hard
Color	white
Flamability according to UL 94	V0
Dimensions (w × h × d)	128.0 mm × 3.3 mm × 12.0 mm
Weight/unit	0.006 kg
PU (units)	5

General ambient conditions

Operation temperature range	-40 °C ... +80 °C
Storage temperature range	-40 °C ... +85 °C
Vibration resistance	0.7 g acc. to EN 60068-2-6
Shock resistance	15 g acc. EN 60068-2-27

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

12.03.2024 • Subject to technical modification

Part No. [716438](#) • Datasheet version: 02

page 1 of 2

Technical data sheet

Load monitoring · LOCC-Box Accessories

Technical data

Rated current	DC 6 A
Pole number	16

Certifications/Standards

Standards	DNVGL-CG-0339 Temperature Class D – not certified Humidity Class B – not certified Vibration Class A – not certified Enclosure Class A – not certified
-----------	--

Dimensions

