


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
11/24/17	A	UPDATED SPECIFICATION	T.B.	B.S.	
04/06/18	B	UPDATED TITLE	T.B.	B.S.	
04/12/19	C	UPDATED TO "ROHS COMPLIANT"	T.B.	B.S.	
06/13/19	D	RATED CURRENT WAS 30A	T.B.	B.S.	
11/26/19	E	RATED CURRENT WAS 20A ADDED WIRE LENGTH	T.B.	B.S.	



NOTES:

1. MATERIAL:
HOUSING : BAKELITE BODY ,UL94V-0, FILE NO. E59481
2. LEAD WIRE IN LOOP: 8" OVERALL LENGTH RED WIRE, 12 AWG,
UL 1015, 600V, 105°C, FLAME RATED VW-1, UL FILE NO. E108485
OR ENGINEERING APPROVED EQUIVALENT
3. RATED CURRENT: 25A
4. ACCEPTS AGC/JMC FUSES
5. INSULATION RESISTANCE AT 500V DC: 100MΩ MIN
6. CONTACT RESISTANCE: 5mΩ AT 1A DC
7. DIELECTRIC STRENGTH FOR 60 SECONDS: AC 2000V MIN
8. ROHS COMPLIANT

Tolerance (Except as noted)	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
	decimal		Scale	Drawn By B.S.
±.5 (.020)				Approved By T.B.
Fractional ± .8 (.030)	Title INLINE FUSE HOLDER AGC/JMC FUSES			
Angular ± 3°	Date 11/26/19	Drawing Number BF302		