


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
01/09/19	A	UPDATED SPECIFICATION	T.B.	B.S.	
04/12/19	B	UPDATED TO "ROHS COMPLIANT"	T.B.	B.S.	
11/26/19	C	WIRE LENGTH WAS 139.70	T.B.	B.S.	



NOTES:

- MATERIAL:
HOUSING : POLYPROPYLENE ,UL94-HB, FILE NO. E85783
- WIRE: 6" LONG RED WIRE, 18 AWG, UL 1015, 600V, 105°C, FLAME RATED VW-1, UL FILE NO. E193578 OR ENGINEERING APPROVED EQUIVALENT
- RATED CURRENT: 10A
- ACCEPTS JMC FUSES: 6.3x30mm (JMC/AGC) Fuses
- INSULATION RESISTANCE AT 500V DC: 100MΩ MIN
- CONTACT RESISTANCE: 5mΩ AT 1A DC
- DIELECTRIC STRENGTH FOR 60 SECONDS: AC 1500V MIN
- ROHS COMPLIANT

Tolerance (Except as noted)	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
	decimal ±.5 (.020)	Scale	Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title INLINE FUSE HOLDER		
Angular ± 3°	Date 11/26/19	Drawing Number BF310	