



Part Number	UNI6B108WH500
Description	UniStrand White Equipment Wire
Conductor Material	Plain Annealed Copper
Insulation	HRPVC (Type T13 to BS EN 50363)
Insulation Radial Thickness	0.60mm (Nominal)
Diameter Over Insulation	Lower Limit: 1.90mm Upper Limit: 2.30mm
Conductor Stranding	1/0.80mm
Conductor Cross Section Area	0.5mm ²
Voltage Rating	1/0.80mm
Cable Weight	0.87kg per reel
Temperature Range	15 to +105 °C
Length Supplied	500m +/- 10-12%
Applicable Standards	BS EN 50525-2-31 Section 5.3 Table B.3

