



Part Number	UNI6B108GNYW100
Description	UniStrand Green/Yellow Equipment Wire
Conductor Material	Plain Annealed Copper
Insulation	HRPVC (Type T13 to BS EN 50363)
Insulation Radial Thickness	0.60mm (Nominal)
Diameter Over Insulation	Lower Limit: 1.90mm Upper Limit: 2.30mm
Conductor Stranding	1/0.80mm
Conductor Cross Section Area	0.5mm ²
Voltage Rating	300V/500V
Cable Weight	0.87kg per reel
Temperature Range	-15 to +105 °C
Length Supplied	100m +/- 10-12%
Applicable Standards	-15 to +105 °C