



Oclip

CLIP IT ON, LIGHT IT UP

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
300 lumens	30 hours	70 meters

*This information is for market reference only. Please do not make it public.



▲ Black

MARKET APPLICATIONS

Everyday Carry
Outdoors
Emergency

UPC : 6975498002703 (Black)

DESCRIPTION

Oclip is a compact and versatile EDC clip-on light that allows users to clip, hang, or magnetically attach it to iron objects. It has extensive application scenarios, including hiking, photo fill light, cycling, reading, and safety warning. Equipped with a durable spring clip, it overcomes the shortcomings of metal fatigue and deformation in traditional back clips, providing a more stable grip capable of clamping onto thicker objects. The product has a maximum brightness of up to 300 lumens and supports Type-C charging. It also features a red-light warning function to ensure user safety.



FEATURES

- **Dual light sources:** White light for daily use and red light for night vision. The beacon mode in white light and the red blink mode ensure that users stay visible in critical moments.
- **Multiple ways to carry:** The versatile clip enables users to clip, hang, or magnetically attach the light to iron objects. It has extensive application scenarios, such as hiking, providing fill light for photos, cycling, reading, and safety warnings.
- **Durable clip:** The durable clip has passed 10,000 cyclic tests, overcoming the shortcomings of metal fatigue and deformation found in traditional back clips. It provides a more stable grip and can clamp objects up to 14mm thick.
- **Lightweight and Compact:** Weight: 1.05oz / 30g; Length: 1.90in / 48.5mm; Width: 0.82in / 21mm.

OUTPUT

SPECIFICATIONS	High	Medium	Low	Moonlight	Red Light
	300 ± 180 lumens	100 lumens	10 lumens	1.5 lumens	4 lumen
	1+60 minutes	90 minutes	12 hours	30 hours	5 hours
	70 meters	40 meters	10 meters	N/A	N/A
	1,300 cd	450 cd	40 cd	N/A	N/A
	White Strobe: 13Hz@300lm Red Strobe: 1Hz@4lm Signal Strobe: 0.33Hz@300lm				

* All data above are test results according to ANSI/NEMA FL 1-2009 standards.

LIGHT SOURCE

White: High-Performance LED (CCT: 5700-6500K)
 Red: TZ-2016 (WL: 620-625nm)

DIMENSIONS

Length: 1.90in / 48.5mm
 Width: 0.82in / 21mm
 Thickness: 0.90in / 23mm

WEIGHT

1.05oz / 30g (Including Battery)

BODY MATERIAL

Aluminum alloy (A6061-T6)

POWERED BY

Customized 280mAh 3.7V
 Rechargeable Battery

WARRANTY

Olight's 2-Year Warranty
 Visit: <https://olightworld.com/olight-warranty>

IN THE BOX

Oclip x 1
 USB-C Charging Cable x 1
 User Manual x 1

WATERPROOF IPX5



DROP TEST



COMPLIANCE



olightworld.com © Olight 08/08/23 V1

Made in China

Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.