










Arkfeld Ultra

Pioneer in Style

WHITE LIGHT MAX OUTPUT	WHITE LIGHT MAX RUNTIME	WHITE LIGHT MAX THROW	UV LIGHT MAX OUTPUT	UV LIGHT MAX RUNTIME	LASER MAX OUTPUT	LASER MAX RUNTIME
						
1,400 Lumens	11 Days	103 Meters	900 mW	315 Minutes	≤5 mW (Class 3R) ≤0.39 mW (Class 1)	61 h (Class 3R) 174 h (Class 1)

* This information is for market reference only. Please DO NOT make it public.



MARKET APPLICATIONS:

EDC (Everyday Carry), Outdoors

UPC:

Arkfeld Ultra Class 1 (Olive Green) CW: 6977261690384

Arkfeld Ultra Class 3R (Olive Green) CW: 6977261690070

DESCRIPTION





Crafted from O-aluminum, an exclusive material invented by Olight that is twice as hard as standard 6061 aluminum alloy, the Arkfeld Ultra boasts exceptional wear and scratch resistance for everyday use. Characterized by angular lines and bold edges, the light is given a unique and striking look. It features a bright white light, a green laser beam, and a UV light, all easily accessible with the selector switch. From presentations to inspecting cleanliness, the Arkfeld Ultra's three lights are perfect for your needs. Furthermore, its sleek flat design and two-way pocket clip make this upgraded light ideal for travel or work. Versatile and incredibly rugged, the Arkfeld Ultra is the ultimate choice for EDC gear.



FEATURES

- **Exceedingly Durable Material:** O-aluminum offers exceptional hardness and wear resistance, ensuring the light maintains its appearance and functionality over time.
- **Sleek and Futuristic Appearance:** Featuring a striking blend of angular lines, sharp edges, and a matte finish, it looks appealing to the eye and feels solid in the hand.
- **Three-in-One Functionality:** Combines white light, UV light, and green laser in one flashlight, perfect for a wide range of applications.
- **Sleek Uni-Body Design:** Slim, ultra-thin profile allows the light to slip easily into your pocket.
- **Bright White Light:** Provides a maximum brightness of 1400 lumens with 5 brightness levels for daily illumination.
- **900 mW UV Light:** Powerful UV light is great for detecting counterfeit money, mineral identification, and cleanliness checks.
- **Convenient Operation:** Easily switch between the three lights using the selector for seamless adjustments.

SPECIFICATIONS

White Light					
	Turbo	High	Medium	Low	Moon
	1,400~420 lumens	420~100 lumens	100 lumens	15 lumens	1 lumen
	4+121 minutes	135+12 minutes	9 h+45 minutes	55 hours	11 days
	103 meters	62 meters	29 meters	11 meters	2 meters
	2,630 cd	971 cd	210 cd	31 cd	1 cd
UV Light			Laser		
Max Output: 900 mW Max Runtime: 5 h 15 min Wavelength: 365~370 nm			Max Output: ≤5 mW (Class 3R) Max Runtime: 61 h Wavelength: 510~530 nm	Max Output: ≤0.39 mW (Class 1) Max Runtime: 174 h Wavelength: 510~530 nm	

* All data above are test results according to ANSI/NEMA FL 1-2019 standards.

LIGHT SOURCES

White Light, UV Light, Green Laser

DIMENSIONS

4.72 x 1.06 x 0.63 in (120 x 27 x 16 mm)

WEIGHT

4.19 oz (119 g) (Including Battery)

BODY MATERIAL

O-Aluminum

POWERED BY

Built-In 1500 mAh Lithium Polymer Battery


WARRANTY

Lifetime Warranty in Australia, China, France, Germany, and the USA.
2-Year Warranty in Other Countries and Regions.


IN THE BOX

Arkfeld Ultra x 1
Magnetic Charging Cable x 1
User Manual x 1



WATERPROOF
IPX7



DROP TEST



COMPLIANCE



olight.com © OLIGHT 07/26/24 V1
Made in China

Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.