

Technische Daten

Size (HxWxD):	37x37x10 mm / 1.46x1.46x0.39 in
Weight:	13 g / 0.44 oz
Mounting:	On a flat surface
Shell material:	Plastic
Shell color:	Black,Mocha,Ivory
Ambient working temperature:	-20 °C to 60 °C /-5 °F to 140 °F
Humidity:	0% to 100% RH
Protection class:	IP54
Power supply:	1x 3 V battery (included)
Battery type:	CR2032
Estimated battery life:	3 years
Bluetooth protocol:	4.2
RF band:	2400 - 2483.5 MHz
Max. RF power:	< 4 dBm
Range:	Up to 30 m / 100 ft outdoors, up to 10 m / 33 ft indoors (depending on local conditions)
Encryption:	AES (CCM mode)