

Installation cable Meridian Install SP215 CPR-Version; 2 x 1,50 mm²; FRNC Ø 6,80 mm; black; Cca

Art. No.: 415-0051FC



General Data

Article number :	415-0051FC
Name :	Meridian Install SP215 CPR-Version
EAN :	4049371375313
Properties :	OFC oxygen free copper
Properties :	FRNC flame retardant
Properties :	Halogen-free / LSZH
Properties :	Analog
Application area :	ELA 100 V
Application area :	Installation
Application area :	Studio / Broadcast
Application :	Installation cable
Application :	Speaker Cable
Colour :	black
BPVo-Euroclass :	Cca

Conductor resistance per 1 km [Ω] :

13

Technical Data

Construction :	(2LIY1,50mm ²)Y
Jacket material :	FRNC
Jacket Ø [mm] :	6,80
Number of Channels (audio) :	1
Inner conductor (audio) :	2
Inner conductor (audio) [mm ²] :	1,50
Inner conductor Ø (audio) [mm] :	1,38
AWG (audio) :	16
Copper strands (audio) :	84
Copper strand Ø (audio) [mm] :	0,15
Conductor insulation Ø [mm] :	2,62
Weight per 1 m [g] :	78
UV-resistant :	yes
Fire load per m [kWh] :	0,29
Style variant :	round
Packing :	500 m spool
Packing :	100 m spool
Temperature min. [°C] :	-30
Temperature max. [°C] :	70
Width [mm] :	6,8
Height [mm] :	6,8

Electrical Data

Capac. cond./cond. per 1 m (audio) [pF] :	150
Insulation resist. per 1 km [GΩ] :	0,005
Insulation resist. per 1 km (audio) [GΩ] :	0,005