

# 45MM DIGITAL GAUGE



FEATURES	
PRESSURE RANGE	0÷16 BAR / 0÷235 PSI
OPERATING TEMPERATURE	-20 ÷ +50 °C (WITHOUT FREEZING)
RESOLUTION RATE	±0,04 BAR / ±0,5PSI
FOUR UNIT DISPLAY	BAR - PSI - KG/CMQ. - KPa
DISPLAY	LIQUID CRYSTAL DIGITAL
POWER	CR2032 BATTERY
POWER SAVING MODE	AUTO SHUT DOWN
SURFACE FINISHING	RUBBER SPRAY PAINT
DIMENSIONS	45x45x31 MM.
REAR INLET	1/8"
WEIGHT	41 GR.

## INSTRUCTION:

Press the "ON/OFF" key until you reach the desired unit of measure (BAR-PSI-KG/CMQ-KPa).

The gauge switches off automatically after approx. 15 secs, alternatively hold the "ON/OFF" key down for 3 secs.

### **Replacing the batteries:**

Take off the cover of battery.

Please kindly note: don't touch the PCB with your hand because it must take with static Electricity.

Use the screwdriver to press the battery down and slip it out.

Put new battery to replace the old.

Please kindly note: wear the gloves or keep your hands no sweat; Otherwise, it maybe make the battery oxidation.

Insert the cover.

Re-use again.

Without pneumatic switch.

The using lifetime is more than 19200 times (80 h).