



Specification

Backing Adhesive	
Material	Rubber
180° Peel Adhesion	>50N/25mm
Tack rolling ball	> #8
Hook & Loop	
Material	100% Nylon
Color	Black
Operating Temperature	-10 ~ 75°C
Melting point	Hook 230°C / Loop 180°C
Tensile Strength	Initial 8.3N/cm ² After 1000 times 6.7N/cm ² After 5000 times 6N/cm ²
Peel Strength	Initial 2.5N/cm After 1000 times 2.1N/cm After 5000 times 1.6N/cm
Stear Strength	110N/cm ²

Other information for Fastener

UV & Chemical Resistance	Yes (under 50% caustic soda, ammonia 28% and 2.5% hydrochloric acid, nitric acid 3.5% or less, can still be effective)
Operating under water	50% Reduction of tensile strength (Can fully restored after drying)
Shrinkage Rate	<2.0%
Water Color Fastness (AATCC 107-1997)	Gerade 3

DATE	REVISION	APPROVAL BY	DIMENSION	mm ±0.5	PART No	STD-LH25/1M
			DRAW BY	Camily	NAME	25mm x 1M Velcro Hook & Loop Set
			APPROVAL BY	Rikki		
			DATE	08-08-2012		