

Speaker cable transparent Datasheet



The Application:
Rated Voltage. 48V

splittable cable

Temperature range min. -20° C
Temperature range max. 70° C

Item No.	Speaker cable transparent	Speaker cable transparent
Jacker, outer dimension	PVC 2.5X5mm	PVC 2.8X5.6mm
Cross section area	2 x 0.75 sqmm	2 x 1.0 sqmm
strand per conductor	24 x 0.2 mm	32 x 0.2 mm
Conductor material	CCA	CCA
color	Transparent	Transparent
AWG	18AWG	17AWG
Packaging	10 meter spool	10 meter spool
Max current	6A	8A
Halogen free	NO	NO

Item No.	Speaker cable	Speaker cable
Jacker, outer dimension	PVC 3.2X6.4mm	PVC 3.5X7mm
Cross section area	2 x 1.5 sqmm	2 x 2.5 sqmm
strand per conductor	48 x 0.2 mm	80 x 0.2 mm
Conductor material	CCA	CCA
color	Transparent	Transparent
AWG	16AWG	13AWG
Packaging	10 meter spool	10 meter spool
Max current	10A	16A
Halogen free	NO	NO