

TOLERANCE UNLESS OTHERWISE SPECIFIED:
±.010 (0.25)




THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

ADD TOLERANCE ±.010 (±0.25)
ADD PLATING SPECS
R.STA.MONICA MAY.26/2015

4




NOTES:

HOUSING: PA66, UL94V-0, COLOR: BLACK

CONTACTS:

PART NO.	MATERIAL & PLATING
A00-108-220-450	0.45MM PHOSPHOR BRONZE GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING
A00-108-620-450	0.35MM COPPER ALLOY 30µIN OF GOLD PLATING ON CONTACT AREA WITH TIN PLATING ON SOLDER AREA ALL OVER NICKEL UNDERPLATING



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.

MODULAR JACK TOP ENTRY PCB
8 POSITIONS



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. A00-108-220-450

DRAWN: R.BLAKEY

DATE: NOV. 13/06

CHECKED:

DATE:

PART NUMBER SEE PART NO.

DRAWING NUMBER

A00-108-220-450

ISSUE

4