




| No. | Changes and/or Note No. | Date | Sign | No. | Changes and/or Note No. | Date | Sign |
|-----|-------------------------|------|------|-----|-------------------------|------|------|
|     |                         |      |      |     |                         |      |      |




| Part Number  | Description  | Pack | ITEM | PART NAME     | Q'ty | NOTES      |
|--------------|--------------|------|------|---------------|------|------------|
|              |              |      | 1    | SCREW         | 3    | M3         |
| 7960-0206-11 | D45ZF09-RG-K | Kit  | 2    | METAL HOOD-1  | 1    | Zinc alloy |
|              |              |      | 3    | WASHER        | 1    |            |
|              |              |      | 4    | SR            | 1    |            |
|              |              |      | 5    | STRAIN RELIEF | 1    |            |
| 7961-0206-11 | D45ZF09-RG   | Bulk | 6    | BOLT          | 2    | UNC 4-40   |
|              |              |      | 7    | LATCH-1       | 1    |            |
|              |              |      | 8    | LATCH-2       | 1    |            |
|              |              |      | 9    | METAL HOOD-2  | 1    | Zinc alloy |

|                    |              |               |               |                                                        |                                                |
|--------------------|--------------|---------------|---------------|--------------------------------------------------------|------------------------------------------------|
| DATE<br>2013-06-13 | DRAWN<br>MRR | SCALE<br>Free | MATERIAL TYPE | GENERAL TOLERANCE<br>X. ±0.60<br>.X ±0.38<br>.XX ±0.25 | ANGLE TOLERANCE<br>X. ±5°<br>.X ±3°<br>.XX ±2° |
|                    | APPROVED     |               | REPLACES      |                                                        |                                                |



**FULL METAL HOOD**  
D45ZF09 - Series  
Side Entry (45°)

DRAWING No.



**6688-9641**