

Model No.: **GP910A**


NO MERCURY ADDED	
Description	: Mercury Free Alkaline Manganese Battery, N Size
Chemical System	: Alkaline Manganese
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: $\phi 12.0$ mm x 30.2 mm
Terminals	: Protruded positive (+) and flat negative (-) contacts
Jacket	: Foil jacket
Applications	: Hearing aid, pager, etc.
Average Weight	: 9g

Cross References:



GP	JIS	IEC	Energizer	Duracell/
910A	LR1	LR1	E90	MN9100

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
20 Ohms	24 Hrs/ Day	0.9V	11.8 Hrs



At 20°C ± 2°C within 30 days of manufacture



Unit : mm

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.
Copyright© GPI International Ltd. - All rights reserved

 **Member**
Gold Peak Group

11100110294