

PH ELECTRODE

Model : PE-03

Features	Economical cost, general purpose, laboratory & field usage.
Measuring Range	1 to 13 pH (typical 0 to 14 pH).
Operation Temperature	5 to 60 °C (41 to 140 °F).
Electrode Structure	Combination type.
Zero Potential for pH Value	7.1 pH.
Body Material	Epoxy.
Connector	BNC.
Mechanical Protection	With protection bottle on the electrode head.
Dimensions	Body length - 160 mm. Body Dia. - 12 mm. Cable length - 1000 mm.
Applications	Water conditioning, aquariums, beverage, fish hatcheries, food processing, photography, laboratory, paper industry, plating industry, quality control, school & college, water conditioning.