

Data Sheet

LiFY Wire 1 x 0.75mm²



Strand per conductor:	0.75 mm ²
No. of conductors:	96 x 0.1mm
Length:	100 meter
Color:	Yellow
Rated voltage:	48V
Rated current:	6A
Jacket, outer dimension:	PVC 2.2 mm
Conductor material:	copper
Conductor structure:	twisted
Insulation material (with thickness):	PVC 0.61 mm
Core diameter:	0.98mm
Insulation resistance:	Min 200M ohm x km
Conductor resistance:	Max 31Ω/KM
Maximum dielectric strength:	1500V / AC
Temperature range:	-20°C to +70°C