

Data Sheet

YV Jumper Wire, 2 x 0.28 mm², 25 M, Red/Black



Technical data

Length: 25 meters

Color: Red/Black

Jacket, outer dimension: PVC 2 x 1.1 mm

Cross section: 2 x 0.28 mm²

No. of conductors: 2 x 0.6 mm²

Conductor material: Copper

Insulation material: PVC

Insulation resistance: Min. 200 Mohm x km

Conductor resistance: Max. 110 ohm/km

Maximum dielectric strength: 800 V AC

Rated voltage: < 50 V AC / 75 V DC

Rated current: 2.2 A

Operating & storage temperature: -20 to +70 °C

Operating & storage humidity: 35 % ~ 95 %